


Grup de preparare aer FRC-1-D-7-O-MAXI-A

Numar piesa: 192649

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	Maxi
Seria	D
Blocaj de actionare	Buton rotativ cu blocare
Pozitie de instalare	vertical +/- 5°
Purjare a condensului	complet automat
Structura constructiva	filtru regulator fara manometru Lubrifiant proportional standard
Cantitate max. de condens	80 cm ³
Finete de filtrare	40 µm
Protectie pahar	Cos metalic de protectie
Indicator de presiune	pregatit G1/4
Presiune de lucru	0.2 MPa...1.2 MPa 2 bar...12 bar
Domeniu de reglare a presiunii	0.5 bar...7 bar
Histerezis max. de presiune	0.04 MPa 0.4 bar 5.8 psi
Debit nominal standard (normalizat conform DIN 1343)	8700 l/min
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [-:~:-:-]
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura medie	-10 °C...60 °C
Temperatura ambianta	-10 °C...60 °C
Greutate produs	2520 g
Tipul de montare	Instalarea liniei cu accesorii
Conector pneumatic 1	G1
Conexiune pneumatica 2	G1
Material carcasa	Zinc turnat sub presiune PC