

Priza
MSSD-EB-S-M14

Numar piesa: 192745

FESTO



Fisa de date

Caracteristica	Valoare
Frecventa de conectare	10
Tipul de montare	pe ventil electromagnetic cu surub central M2,5
Pozitie de instalare	orice
Greutate produs	17 g
Conector electric	4 pini Priza Formular C
Diametrul cablului	4 mm...6 mm
Sectiunea transversala nominala a conductorului	0.25 mm ² ...0.5 mm ²
Tip de protectie	IP67 conform IEC 60529
Temperatura ambianta	-25 °C...90 °C
Conformitatea LABS	VDMA24364-B2-L
Material carcasa	PA
Culoarea carcasei	negru