

Priza
MSSD-C-S-M16
Numar piesa: 192748

FESTO



Fisa de date

Caracteristica	Valoare
Frecventa de conectare	10
Tipul de montare	pe ventil electromagnetic cu surub central M3
Pozitie de instalare	orice
Greutate produs	38 g
Conector electric	4 pini Priza Forma A
Diametrul cablului	5.5 mm...8 mm
Sectiunea transversala nominala a conductorului	0.5 mm ² ...1 mm ²
Tip de protectie	IP67 conform IEC 60529
Temperatura ambianta	-25 °C...90 °C
Conformitatea LABS	VDMA24364-B2-L
Material carcasa	PA
Culoarea carcasei	negru