

Generator vacuum VAD-M5

Numar piesa: 19293

FESTO



Fisa de date

Caracteristica	Valoare
Diametru nominal duza Laval	0.5 mm
Pozitie de instalare	orice
Caracteristicile ejectorului	vid ridicat
Structura constructiva	In forma de T
Presiune de lucru	0.15 MPa...1 MPa 1.5 bar...10 bar 21.75 psi...145 psi
Vacuum max.	80 %
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:4:4]
Nota referitoare la mediul de lucru/comanda	Posibilitatea operarii cu ulei (necesar pentru operare ulterioara)
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura medie	-20 °C...80 °C
Temperatura ambianta	-20 °C...80 °C
Tipul de montare	cu orificiu de trecere
Conector pneumatic 1	M5
Conector pneumatic 3	M5
Racord de vacuum	M5
Material carcasa	Aluminiu turnat sub presiune