


Cilindru plat
DZF-1 1 1/4"- -A-P-A-S20
Numar piesa: 194179

FESTO



Fisa de date

Caracteristica	Valoare
Cursa	0.04 țol...13 țol
Ø piston	1 1/4"
Unghi de rotatie max. a tijei de piston +/-	0.8 grd
Amortizare	inele/placi de amortizare elastice pe ambele parti
Mod de functionare	cu dubla actiune
Siguranta la rasucire/ghidaj	Piston oval
Presiune de lucru	0.1 MPa...1 MPa 1 bar...10 bar
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:4:4]
Nota referitoare la mediul de lucru/comanda	Posibilitatea operarii cu ulei (necesar pentru operare ulterioara)
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-20 °C...80 °C
Fora teoretica la 0,6 MPa (6 bari, 87 psi), debit de retur	415 N
Fora teoretica la 0,6 MPa (6 bari, 87 psi), cursa de avans	415 N
Conexiune pneumatica	1/8 NPT
Material capac	Aluminiu
Material garnituri	FPM TPE-U (PU)
Material carcasa	Aliaj de aluminiu forjat
Material tija de piston	otel aliaj inalt