

Teava
PQ-AL-28X1,5X3000
Numar piesa: 194593

FESTO



Fisa de date

Caracteristica	Valoare
Ø exterior	28 mm
Ø interior	25 mm
Presiune de lucru in functie de temperatura	-0.95 bar...10 bar
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura medie	-25 °C...75 °C
Temperatura ambianta	-30 °C...75 °C
Greutatea produsului in functie de lungime	0.337 kg/m
Culoare	argintiu
Nota privind materialele	Conform RoHS
Material furtun	Aliaj de aluminiu forjat