

Suport lagar CRLMC-50

Numar piesa: 197322

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	50
Pe baza standardului	ISO 15552 (anterior si VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Pozitie de instalare	orice
Clasa de rezistenta la coroziune KBK	4 - Mediu coroziv deosebit de puternic
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-40 °C...80 °C
Greutate produs	254 g
Nota privind materialele	Conform RoHS
Material fixare	electrolizata otel inalt aliat
Material rulment	Material plastic