

## Suport lagar CRLMC-63

Numar piesa: 197323

**FESTO**



## Fisa de date

| Caracteristica                       | Valoare                                                               |
|--------------------------------------|-----------------------------------------------------------------------|
| Dimensiune                           | 63                                                                    |
| Pe baza standardului                 | ISO 15552 (anterior si VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290) |
| Pozitie de instalare                 | orice                                                                 |
| Clasa de rezistenta la coroziune KBK | 4 - Mediu coroziv deosebit de puternic                                |
| Conformitatea LABS                   | VDMA24364-B2-L                                                        |
| Temperatura ambianta                 | -40 °C...80 °C                                                        |
| Greutate produs                      | 306 g                                                                 |
| Nota privind materialele             | Conform RoHS                                                          |
| Material fixare                      | electrolizata<br>otel inalt aliat                                     |
| Material rulment                     | Material plastic                                                      |