

# Amortizor de zgomot UO-1/8

Numar piesa: 197583

FESTO



## Fisa de date

| Caracteristica                        | Valoare                                       |
|---------------------------------------|-----------------------------------------------|
| Pozitie de instalare                  | orice                                         |
| Structura constructiva                | Amortizor de zgomot deschis                   |
| Presiune de lucru                     | 0 MPa...0.8 MPa<br>0 bar...8 bar              |
| Mediu de operare                      | Aer comprimat conform ISO 8573-1:2010 [7:4:4] |
| Conformitatea LABS                    | VDMA24364-B1/B2-L                             |
| Temperatura ambianta                  | -10 °C...60 °C                                |
| Greutate produs                       | 5 g                                           |
| Conexiune pneumatica                  | G1/8                                          |
| Material insertie amortizor de zgomot | PE                                            |
| Material pivot de insurubare          | PE                                            |
| Nota privind materialele              | Conform RoHS                                  |