

Tub spiralat DUO PUN-10X1,5-S-1-DUO-BS

Numar piesa: 197626

FESTO



Fisa de date

Caracteristica	Valoare
Lungime de lucru	1 m
Ø exterior	10 mm
Lungimea blocului	0.41 m
Ø interior	7 mm
Diametrul bobinajului	80 mm
Numar bobinaje	9.5
Presiune de lucru in functie de temperatura	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Autorizare	TÜV
Organizatia emitenta a certificatului	B 013277 0506 00
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-]
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-35 °C...60 °C
Greutate produs	220 g
Conexiune pneumatica	pentru conector cu Ø exterior de 10 mm
Culoare	albastru/negru
Duritate Shore	D 52 +/-3
Material furtun	TPE-U (PU)