

Piulita olandeza MCK-PK-13

Numar piesa: 206504

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	Filet interior M22x1
Presiune de functionare interval complet de temperatura	-0.095 MPa...1.2 MPa -0.95 bar...12 bar -13.775 psi...174 psi
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-10 °C...60 °C
Conector pneumatic 1	pentru niplu de legatura, Ø interior 13 mm cu piulita olandeza
Material piulita olandeza	Aliaj de aluminiu forjat, anodizat
Nota privind materialele	Conform RoHS