

Prize de cuplare KD3-1/8-A

Numar piesa: 2142

FESTO



Fisa de date

Caracteristica	Valoare
Latimea nominala	4.95 mm
Presiune de functionare interval complet de temperatura	-0.095 MPa...1.2 MPa -0.95 bar...12 bar -13.775 psi...174 psi
Debit nominal standard (normalizat conform DIN 1343)	185 l/min...572 l/min
Debitul nominal standardizat conform ISO 8778	200.5 l/min...620 l/min
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:::]
Nota referitoare la mediul de lucru/comanda	Este posibila functionarea cu ulei
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-10 °C...60 °C
Cuplu de strangere nominal	5 Nm
Toleranta fata de cuplul de strangere nominal	± 15 %
Greutate produs	28 g
Conector pneumatic 1	Filet exterior G1/8
Nota privind materialele	Conform RoHS
Material garnituri	NBR
Material arc	otel inoxidabil aliaj inalt
Material carcasa	Alama, nichelata
Material garnitura de filet	PA66-GF30 / TPE-U
Material piesa filetata	Alama, nichelata
Material bila	otel inoxidabil inalt aliat
Material saiba elastica	Otel inoxidabil aliaj inalt
Material corp ventil	Alama
Manson de deblocare a materialului	Alama, nichelata