


Angrenaj|cutie de viteze|reductor|transmisie
EMGA-40-P-G5-EAS-40

Numar piesa: 2297685

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiunea flansei reductorului	40 mm
Dimensiune flansa motor	40 mm
Joc de rasucire	0.25 grd
Tipul de reductor	Reductor planetar
Raportul de transmisie	5:1
Turatie de lucru max.	18000 1/min
Temperatura de functionare unitate actionare	-25 °C...90 °C
Conformitatea LABS	VDMA24364-B2-L
Tip de protectie	IP54
Cuplu de iesire continuu	14 Nm
Momentul de inertie al reductorului	0.019 kgcm ²
Cuplu de iesire max.	22 Nm
Randament max.	98 %
Rigiditate la torsiune	1 Nm/arcmin
Greutate produs	350 g
Interfata de iesire la unitatea de actionare	40G
Interfata reductor unitate de actionare	40P
Nota privind materialele	Conform RoHS