

Manson de prindere EAMH-60-8-C18.1

Numar piesa: 2428517

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	60
Pozitie de instalare	orice
Turatie max.	6000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-10 °C...60 °C
Momentul de inertie al masei	1.44 kgmm ²
Greutate produs	34 g
Nota privind materialele	Conform RoHS