

Manson de prindere EAMH-110-19-C34

Numar piesa: 2429559

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	110
Pozitie de instalare	orice
Turatie max.	5000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-10 °C...60 °C
Momentul de inertie al masei	29.9 kgmm ²
Greutate produs	188 g
Nota privind materialele	Conform RoHS