

Placa racordare VABS-S7-BE-B-G14-VDE1

Numar piesa: 2999476

FESTO



Fisa de date

Caracteristica	Valoare
Pozitie de instalare	orice
Alimentarea cu aer pilot	intern
Presiune de lucru	0.2 MPa...0.8 MPa 2 bar...8 bar
Debit de ventilare Kv	2.2 m³/h
Debit Kv, aerisire	8.6 m³/h
Protectie la explozie	Zona 1 (ATEX) Zona 2 (ATEX) Zona 21 (ATEX) Zona 22 (ATEX)
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [:-:~:-:~:-]
Clasa de rezistenta la coroziune KBK	4 - Mediu coroziv deosebit de puternic
Conformitatea LABS	VDMA24364 zona III
Tip de protectie	IP65
Greutate produs	250 g
Tipul de montare	cu orificiu de trecere
Conector pneumatic 1	G1/4
Conexiune pneumatica 2	VDI/VDE 3845 (NAMUR)
Conector pneumatic 3	G1/4
Nota privind materialele	Conform RoHS
Materialul placii de racordare	Aluminiu ematalizat
Material garnituri	NBR