

Flansa oscilanta SZB-40

Numar piesa: 30799

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	40
Pozitie de instalare	orice
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-40 °C...90 °C
Greutate produs	288 g
Nota privind materialele	Conform RoHS
Material fixare	otel inoxidabil aliaj inalt
Material bolt	Otel galvanizat
Material rulment	Material plastic
Material suruburi	Otel, galvanizat
Material siguranta	Otel cu arc, galvanizat