

Suport lagar LSNG-40

Numar piesa: 31741

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	40
Pe baza standardului	VDMA 24562
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-40 °C...150 °C
Sarcina admisibila maxima	1.5 kN
Greutate produs	228 g
Nota privind materialele	Conform RoHS
Material fixare	otel inalt aliat
Material rulment articulat	Otel PTFE