

Suport lagar LSNG-50

Numar piesa: 31742

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	50
Pe baza standardului	VDMA 24562
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-40 °C...150 °C
Sarcina admisibila maxima	2.5 kN
Greutate produs	416 g
Nota privind materialele	Conform RoHS
Material fixare	otel inalt aliat
Material rulment articulat	Otel PTFE