

Suport lagar LSNG-63

Numar piesa: 31743

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	63
Pe baza standardului	VDMA 24562
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-40 °C...150 °C
Sarcina admisibila maxima	4 kN
Greutate produs	541 g
Nota privind materialele	Conform RoHS
Material fixare	Fonta ductila
Material rulment articulat	Otel PTFE