

Suport lagar LSNG-100

Numar piesa: 31745

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	100
Pe baza standardului	VDMA 24562
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-40 °C...150 °C
Sarcina admisibila maxima	9 kN
Greutate produs	1358 g
Nota privind materialele	Conform RoHS
Material fixare	Fonta ductila
Material rulment articulat	Otel PTFE