

Suport lagar transv. LQG-40

Numar piesa: 31769

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	40
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-40 °C...150 °C
Sarcina admisibila maxima	1.5 kN
Greutate produs	369 g
	13 oz
Nota privind materialele	Conform RoHS
Material fixare	Otel inoxidabil turnat
Material bolt	Otel de calire
Material siguranta	Otel de arcuri