

Suport lagar transv. LQG-80

Numar piesa: 31772

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	80
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-40 °C...150 °C
Sarcina admisibila maxima	6 kN
Greutate produs	1126 g
Nota privind materialele	Conform RoHS
Material fixare	Fonta ductila
Material bolt	Otel de calire
Material siguranta	Otel de arcuri