

Cuplaj
EAMC-67-62-24-25
Numar piesa: 3187895

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	24 mm
Diametru de montare 2	25 mm
Dimensiune	67
Lungime nominala	62 mm
Pozitie de instalare	orice
Turatie max.	4500 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...60 °C
Momentul de inertie al masei	280 kgmm ²
Cuplu transmisibil	143 Nm
Greutate produs	435 g
Nota privind materialele	Conform RoHS