

Talpa fixare DAMH-Q12-40

Numar piesa: 3371846

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	40
Pozitie de instalare	orice
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	0 °C...60 °C
Cuplu de strangere max.	18 Nm
Greutate produs	529 g
Tipul de montare	cu orificiu de trecere
Nota privind materialele	Conform RoHS
Material echer	Otel galvanizat