

Suport lagar LNG-32

Numar piesa: 33890

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	32
Pe baza standardului	ISO 15552 (anterior si VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-40 °C...80 °C
Sarcina admisibila maxima	0.9 kN
Greutate produs	133 g
Nota privind materialele	Conform RoHS
Material fixare	Otel calit
Material rulment	PA