

Bobina
MSFG-24/42-50/60-DS-OD
Numar piesa: 34412

FESTO



Fisa de date

Caracteristica	Valoare
Pozitie de instalare	orice
Indicatorul pozitiei de comutare	nu
Ora min. de preluare	10 ms
Ciclu de lucru	100%
Factorul de putere cos {phi}	0.7
Caracteristici bobina	24 V CC: 4,5 W 42 V CA: 50/60 Hz, putere de preluare 9,0 VA, putere de mentinere 7,0 VA
Fluctuatii de frecventa admise	+/- 5 %
Fluctuatii de tensiune admise	+/- 10 %
Conformitatea LABS	VDMA24364-C1-L
Tip de protectie	IP65
Temperatura ambianta	-5 °C...40 °C
Cuplu max. de strangere priza	0.4 Nm
Greutate produs	55 g
Conector electric	conform DIN EN 175301-803
Tipul de montare	cu piulita randalinata
Nota privind materialele	Conform RoHS
Material bobina	Duroplast Cupru Otel
Material infasurare	Cupru