


Unitate ghidare FENG-50-160-KF

Numar piesa: 34508

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	50
Cursa	160 mm
Pozitie de instalare	orice
Ghidaj	Ghidaj cu bile de recirculare
Structura constructiva	Ghidaj
Protectie la explozie	Respectati informatiile din certificat
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-20 °C...80 °C
Forta max. Fy	1260 N
Forta max. Fy statica	1600 N
Forta max. Fz	1260 N
Forta max. Fz statica	1600 N
Moment max. Mx	65 Nm
Moment max. Mx static	83 Nm
Max. Moment My	70 Nm
Moment My static max.	89 Nm
Moment max. Mz	70 Nm
Moment Mz static max.	89 Nm
Forta de deplasare	15 N
Greutate produs	4814 g
Tipul de montare	cu filet interior
Nota privind materialele	Conform RoHS
Material element de ghidare	Otel calit
Material carcasa	Aliaj de aluminiu forjat, anodizat
Material placa de jug	Aliaj de aluminiu forjat, anodizat