

Unitate ghidare FENG-63-50-KF

Numar piesa: 34513

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	63
Cursa	50 mm
Pozitie de instalare	orice
Ghidaj	Ghidaj cu bile de recirculare
Structura constructiva	Ghidaj
Protectie la explozie	Respectati informatiile din certificat
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-20 °C...80 °C
Forta max. Fy	1260 N
Forta max. Fy statica	1600 N
Forta max. Fz	1260 N
Forta max. Fz statica	1600 N
Moment max. Mx	75 Nm
Moment max. Mx static	95 Nm
Max. Moment My	90 Nm
Moment My static max.	115 Nm
Moment max. Mz	90 Nm
Moment Mz static max.	115 Nm
Forta de deplasare	15 N
Greutate produs	5655 g
Tipul de montare	cu filet interior
Nota privind materialele	Conform RoHS
Material element de ghidare	Otel calit
Material carcasa	Aliaj de aluminiu forjat, anodizat
Material placa de jug	Aliaj de aluminiu forjat, anodizat