

## Ventuză vacuum VAS-100-1/4-NBR

Numar piesa: 34586

FESTO



### Fisa de date

| Caracteristica                                  | Valoare                                                        |
|-------------------------------------------------|----------------------------------------------------------------|
| Latimea nominala                                | 4 mm                                                           |
| Diametrul ventuzei                              | 100 mm                                                         |
| Diametru de aspiratie eficient                  | 85 mm                                                          |
| Pozitie de conectare                            | sus                                                            |
| Forma de ventuza                                | rotund plat                                                    |
| Presiune de lucru                               | -0.095 MPa...0 MPa<br>-0.95 bar...0 bar<br>-13.775 psi...0 psi |
| Presiunea nominala de functionare               | -0.07 MPa<br>-0.7 bar<br>-10.15 psi                            |
| Mediu de operare                                | aer atmosferic conform ISO 8573-1:2010 [7:::]                  |
| Conformitatea LABS                              | VDMA24364-A1-L                                                 |
| Temperatura ambianta                            | -20 °C...80 °C                                                 |
| Fora de smulgere la 70 % vacuum                 | 397 N                                                          |
| Fora de mentinere la presiune de lucru nominala | 397 N                                                          |
| Filet de fixare                                 | G1/4                                                           |
| Fixarea ventuzei                                | G 1/4                                                          |
| Racord de vacuum                                | G1/4                                                           |
| Culoare                                         | negru                                                          |
| Duritate Shore                                  | 70 +/- 5                                                       |
| Material pivot de insurubare                    | Zinc turnat sub presiune                                       |
| Nota privind materialele                        | Conform RoHS                                                   |
| Material ventuze                                | NBR                                                            |