

Bobina
VACC-S18-70-K5-1-U2D
Numar piesa: 3546816

FESTO



Fisa de date

Caracteristica	Valoare
Tip de actionare	electric
Pozitie de instalare	orice
Indicatorul pozitiei de comutare	nu
Ciclu de lucru	100%
Clasa de izolare	H
Caracteristici bobina	24 V CC: 7,0 W
Fluctuatii de tensiune admise	-15 % / +10 %
Protectie Ex certificata in afara UE	Clasa I, Div. 2 (CA) Clasa I, Div. 2 (SUA)
Protectie la explozie	Clasa I, Div. 2 (CA) Clasa I, Div. 2 (SUA)
Temperatura ambientala Ex	T4A, 120°C: -25°C <= Ta <= +80°C
Clasa de rezistenta la coroziune KBK	4 - Mediu coroziv deosebit de puternic
Conformitatea LABS	VDMA24364 zona III
Tip de protectie	IP65
Greutate produs	1700 g
Conector electric	Cutie de borne, filet de intrare cablu NPT1/2
Nota privind materialele	Conform RoHS
Material bobina	Aliaj de aluminiu forjat Fonta