

Compensator de moment DARD-L8-40-S

Numar piesa: 4448222

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	32/40
Abatere radiala +/-	2.5 mm
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	0 °C...60 °C
Sarcina maxima admisibila pe termen scurt in directia fortei +/-	3000 N
Sarcina maxim admisibila pe termen lung in directia fortei +/-	1400 N
Greutate produs	109 g
Nota privind materialele	Conform RoHS fara cupru
Material adaptor	Aluminiu, anodizat
Material suruburi	Otel, galvanizat