

Cuplaj EAMD-21-15-12-8X10

Numar piesa: 4820335

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	12 mm
Diametru de montare 2	8 mm
Dimensiune	21
Lungime nominala	15 mm
Pozitie de instalare	orice
Turatie max.	10000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...60 °C
Momentul de inertie al masei	0.45 kgmm ²
Cuplu transmisibil	2 Nm
Greutate produs	13.5 g
Nota privind materialele	Conform RoHS