

Fus de arbore DARF-Q11-35/40

Numar piesa: 4835939

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	35 40
pentru Ø piston	Ø35 Ø40
Structura constructiva	Fus de arbore
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-10 °C...60 °C
Greutate produs	350 g
Tipul de montare	cu orificiu de trecere si bucsa de centrare
Nota privind materialele	Conform RoHS
Material suruburi	Otel, nichelat