

Flansa conectare DARF-Q12-32

Numar piesa: 4886224

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	32
Pozitie de instalare	orice
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	0 °C...60 °C
Cuplu de strangere max.	2.9 Nm
Greutate produs	92 g
Nota privind materialele	Conform RoHS
Material flansa	Aliaj de aluminiu forjat, anodizat
Material suruburi	Otel, galvanizat