

Amortizor de zgomot U-PK-4

Numar piesa: 4932

FESTO



Fisa de date

Caracteristica	Valoare
Pozitie de instalare	orice
Presiune de lucru	0 MPa...1 MPa 0 bar...10 bar
Debit in raport cu atmosfera	580 l/min
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-]
Nota referitoare la mediul de lucru/comanda	Este posibila functionarea cu ulei
Conformitatea LABS	VDMA24364-B1/B2-L
Nivel de presiune acustica	77 dB(A)
Temperatura ambianta	-10 °C...70 °C
Greutate produs	4.1 g
Conexiune pneumatica	PK-4
Material insertie amortizor de zgomot	Bronz
Material pivot de insurubare	Alama
Nota privind materialele	Conform RoHS