


Cuplaj EAMD-75-51-40-32X32-U

Numar piesa: 5078084

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	40 mm
Diametru de montare 2	32 mm
Dimensiune	75
Lungime nominala	51 mm
Pozitie de instalare	orice
Turatie max.	4500 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...60 °C
Momentul de inertie al masei	425 kgmm ²
Cuplu transmisibil	200 Nm
Greutate produs	741 g
Nota privind materialele	Conform RoHS