

Cuplaj
EAMD-56-54-19-23X27
Numar piesa: 5215476

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	19 mm
Diametru de montare 2	23 mm
Dimensiune	56
Lungime nominala	54.5 mm
Pozitie de instalare	orice
Turatie max.	5500 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...60 °C
Momentul de inertie al masei	172 kgmm ²
Cuplu transmisibil	60 Nm
Greutate produs	464 g
Nota privind materialele	Conform RoHS