

# Ventuza vacuum ESS-80-GT-G1/4-I

Numar piesa: 525984

FESTO



## Fisa de date

| Caracteristica                                   | Valoare                                       |
|--------------------------------------------------|-----------------------------------------------|
| Compensarea inaltimii suport de ventuza          | 7.5 mm                                        |
| Raza min. a piesei de prelucrat                  | 100 mm                                        |
| Latimea nominala                                 | 5.5 mm                                        |
| Diametrul ventuzei                               | 80 mm                                         |
| Volum de aspiratie                               | 28.6 cm <sup>3</sup>                          |
| Pozitie de instalare                             | orice                                         |
| Structura constructiva                           | rotund, in forma de clopot                    |
| Forma de ventuza                                 | rotund adanc                                  |
| Presiune de lucru                                | -0.95 bar...0 bar                             |
| Presiunea nominala de functionare                | -0.7 bar                                      |
| Mediu de operare                                 | aer atmosferic conform ISO 8573-1:2010 [7:::] |
| Clasa de rezistenta la coroziune KBK             | 2 - Solicitare moderata din cauza coroziunii  |
| Conformitatea LABS                               | VDMA24364-A1-L                                |
| Temperatura ambianta                             | -10 °C...80 °C                                |
| Fora de smulgere la 70 % vacuum                  | 245 N                                         |
| Fora de mentinere la presiune de lucru nominala  | 245 N                                         |
| Cuplu de strangere max. filet de fixare          | 11 Nm                                         |
| Fora transversala la presiunea de lucru nominala | 99 N                                          |
| Greutate produs                                  | 61 g                                          |
| Tipul de montare                                 | prin racordul de vid                          |
| Racord de vacuum                                 | G1/4                                          |
| Culoare                                          | rosu maro                                     |
| Duritate Shore                                   | 72 +/- 5                                      |
| Material pivot de insurubare                     | Aliaj de aluminiu forjat                      |
| Nota privind materialele                         | Conform RoHS                                  |
| Material ventuze                                 | Vulkollan                                     |