


Ventuza vacuum ESS-80-GT-G1/4

Numar piesa: 525985

FESTO



Fisa de date

Caracteristica	Valoare
Compensarea inaltimii suport de ventuza	7.5 mm
Raza min. a piesei de prelucrat	100 mm
Latimea nominala	5.5 mm
Diametrul ventuzei	80 mm
Volum de aspiratie	28.6 cm ³
Pozitie de instalare	orice
Structura constructiva	rotund, in forma de clopot
Forma de ventuza	rotund adanc
Presiune de lucru	-0.95 bar...0 bar
Presiunea nominala de functionare	-0.7 bar
Mediu de operare	aer atmosferic conform ISO 8573-1:2010 [7:::]
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-A1-L
Temperatura ambianta	-10 °C...80 °C
Fora de smulgere la 70 % vacuum	245 N
Fora de mentinere la presiune de lucru nominala	245 N
Cuplu de strangere max. filet de fixare	11 Nm
Fora transversala la presiunea de lucru nominala	99 N
Greutate produs	60 g
Tipul de montare	prin racordul de vid
Racord de vacuum	G1/4
Culoare	rosu maro
Duritate Shore	72 +/- 5
Material pivot de insurubare	Aliaj de aluminiu forjat
Nota privind materialele	Conform RoHS
Material ventuze	Vulkollan