

Ventuza vacuum ESS-40-BT-G1/4-I

Numar piesa: 525991

FESTO



Fisa de date

Caracteristica	Valoare
Compensarea inaltimii suport de ventuza	9 mm
Raza min. a piesei de prelucrat	35 mm
Latimea nominala	2.5 mm
Diametrul ventuzei	40 mm
Volum de aspiratie	9.8 cm ³
Pozitie de instalare	orice
Forma de ventuza	burduf rotund de 1,5 ori
Presiune de lucru	-0.95 bar...0 bar
Presiunea nominala de functionare	-0.7 bar
Mediu de operare	aer atmosferic conform ISO 8573-1:2010 [7:-:-]
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-A1-L
Temperatura ambianta	-10 °C...80 °C
Fora de mentinere la presiune de lucru nominala	59 N
Fora transversala la presiunea de lucru nominala	22 N
Greutate produs	19 g
Tipul de montare	prin racordul de vid
Racord de vacuum	G1/4
Culoare	rosu maro
Duritate Shore	72 +/- 5
Material pivot de insurubare	Aliaj de aluminiu forjat
Nota privind materialele	Conform RoHS
Material ventuze	Vulkollan