


Set manometru DPA-100-10-MA-SET

Numar piesa: 526098

FESTO



Fisa de date

Caracteristica	Valoare
Conform cu standardul	EN 837-1
Dimensiune nominala, manometru	40
Structura constructiva	Manometru cu tub Bourdon
Tipul de montare	cu filet exterior
Presiune de lucru	10 bar
Clasa de precizie de masurare	2,5
Tip de protectie	IP43
Temperatura ambianta	5 °C...60 °C
Conformitatea LABS	VDMA24364-B1/B2-L
Pozitie de instalare	orice
Conexiune pneumatica	G1/4
Greutate produs	305 g