

Manometru
MA-50-1,6-R1/4-MPA-E-RG
Numar piesa: 526782

FESTO



Fisa de date

Caracteristica	Valoare
Interval de afisare	0 MPa...1.6 MPa
Conform cu standardul	EN 837-1
Dimensiune nominala, manometru	50
Protectie la explozie	Respectati informatiile din certificat Zona 1 (ATEX) Zona 2 (ATEX) Zona 21 (ATEX) Zona 22 (ATEX)
Structura constructiva	Manometru cu tub Bourdon
Tipul de montare	Instalarea liniei
Mediu de operare	Gaze inerte lichide neutre
Nota referitoare la mediul de lucru/comanda	fara acetilena fara oxigen
Presiune de lucru	0 MPa...1.6 MPa 0 bar...16 bar 0 psi...232 psi
Factor de incarcare alternanta	0.66
Clasa de precizie de masurare	2,5
Tip de protectie	IP43
Temperatura medie	-20 °C...60 °C
Temperatura ambianta	-20 °C...60 °C
Conformitatea LABS	VDMA24364-B1/B2-L
Nota privind materialele	Conform RoHS
Pozitie de conectare	Partea din spate, centrat
Conexiune pneumatica	R1/4
Materiale care intra in contact cu mediul	Alama
Material pivot de insurubare	Alama
Material carcasa	ABS
Material vizor	PMMA

Caracteristica	Valoare
Culoarea carcasei	negru
Greutate produs	75 g
Scala	Scara unica MPa (exterior)