

Cuplaj
EAMC-B-15-22-5-5
Numar piesa: 530085

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	5 mm
Diametru de montare 2	5 mm
Dimensiune	15
Lungime nominala	22 mm
Pozitie de instalare	orice
Turatie max.	12000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...60 °C
Momentul de inertie al masei	0.13 kgmm ²
Cuplu transmisibil	1 Nm
Greutate produs	6 g
Nota privind materialele	Conform RoHS