

Prize de cuplare KD4-1/4-I

Numar piesa: 531636

FESTO



Fisa de date

Caracteristica	Valoare
Latimea nominala	7.2 mm
Presiune de functionare interval complet de temperatura	-0.095 MPa...1.2 MPa -0.95 bar...12 bar -13.775 psi...174 psi
Debit nominal standard (normalizat conform DIN 1343)	257 l/min...1292 l/min
Debitul nominal standardizat conform ISO 8778	278.6 l/min...1400.5 l/min
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-]
Nota referitoare la mediul de lucru/comanda	Este posibila functionarea cu ulei
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-10 °C...60 °C
Cuplu de strangere nominal	9.5 Nm
Toleranta fata de cuplul de strangere nominal	± 15 %
Greutate produs	88 g
Conector pneumatic 1	Filet interior G1/4
Nota privind materialele	Conform RoHS
Material garnituri	NBR
Material arc	otel inoxidabil aliaj inalt
Material carcasa	Alama, nichelata
Material piesa filetata	Alama, nichelata
Material inel interior	Alama
Material saiba elastica	Otel inoxidabil aliaj inalt
Material stifturi	Otel inalt aliat, inoxidabil
Material corp ventil	Alama
Manson de deblocare a materialului	PP