

Stecher FBS-SUB-9-GS-DP-B

Numar piesa: 532216

FESTO



Fisa de date

Caracteristica	Valoare
Latime	20 mm
Inaltime	62 mm
Lungime	61 mm
Protocol	PROFIBUS
Elemente de comanda	Comutator DIL
Functii suplimentare	Deconectarea segmentului bus de continuare
Greutate produs	60 g
Interfata Fieldbus	2x 2 cleme cu arc
Diametrul admisibil al cablului	5 mm...10 mm
Tip de protectie	IP65 IP67 in stare asamblata conform IEC 60529
Temperatura ambianta	0 °C...50 °C
Temperatura de depozitare	-20 °C...70 °C
Umiditate relativa	95 % fara condensare
Conformitatea LABS	VDMA24364-B2-L
Nota privind materialele	Conform RoHS
Material carcasa	Ranforsat cu PA
Material piulita olandeza	Alama
Material suruburi	Otel
Material garnituri	NBR