

Stecher FBS-SUB-9-GS-IB-B

Numar piesa: 532217

FESTO



Fisa de date

Caracteristica	Valoare
Latime	20 mm
Inaltime	62 mm
Lungime	61 mm
Protocol	Interbus®
Functii suplimentare	Punte RBST integrat
Greutate produs	60 g
Interfata Fieldbus	1x 5 cleme cu arc
Diametrul admisibil al cablului	5 mm...10 mm
Tip de protectie	IP65 IP67 in stare asamblata conform IEC 60529
Temperatura ambianta	0 °C...50 °C
Temperatura de depozitare	-20 °C...70 °C
Umiditate relativa	95 % fara condensare
Conformitatea LABS	VDMA24364-B2-L
Nota privind materialele	Conform RoHS
Material carcasa	Ranforsat cu PA
Material piulita olandeza	Alama
Material suruburi	Otel
Material garnituri	NBR