


Combinatie filtre fine LFMBA-1/4-D-MINI-DA

Numar piesa: 532864

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	Mini
Seria	D
Pozitie de instalare	vertical +/- 5°
Finete de filtrare	0.01 µm
Eficienta filtru	99.9999 %
Purjare a condensului	rotire manuala
Structura constructiva	Filtru de fibre
Cantitate max. de condens	22 ml
Protectie pahar	Cos metalic de protectie
Presiune de lucru	0.1 MPa...1.6 MPa 1 bar...16 bar 14.5 psi...232 psi
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [6:8:4] Gaze inerte
Conformitatea LABS	VDMA24364-B1/B2-L
Clasa de puritate a aerului la iesire	Aer comprimat conform ISO 8573-1:2010 [1:7:2] Gaze inerte
Temperatura medie	1.5 °C...60 °C
Continut de ulei rezidual	0.01 mg/m³
Temperatura ambianta	-10 °C...60 °C
Greutate produs	651 g
Tipul de montare	Instalarea liniei cu accesorii
Conector pneumatic 1	G1/4
Conexiune pneumatica 2	G1/4
Nota privind materialele	Conform RoHS
Material filtru	Fibra de borosilicat
Material carcasa	Zinc turnat sub presiune PC