

Conexiune bus
FBA-2-M12-5POL-RK

Numar piesa: 533118

FESTO



Fisa de date

Caracteristica	Valoare
Greutate produs	80 g
Interfata Fieldbus	Priza si stecher, M12x1, 5 pini, codificare B
Tip de protectie	IP65 conform IEC 60529
Temperatura ambianta	0 °C...50 °C
Temperatura de depozitare	-20 °C...70 °C
Umiditate relativa	95 % fara condensare
Conformitatea LABS	VDMA24364-B2-L
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Material garnituri	NBR