

Capac inspectare AK-SUB-9/15-B

Numar piesa: 533334

FESTO



Fisa de date

Caracteristica	Valoare
Greutate produs	20 g
Tip de protectie	IP65 IP67 in stare asamblata conform IEC 60529
Temperatura ambianta	-5 °C...50 °C
Conformitatea LABS	VDMA24364-B2-L
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Material suruburi	Otel galvanizat
Material garnituri	NBR
Material capac	PA
Umiditate relativa	fara condensare